



Main

Range	Actassi
Product or component type	Power distribution rail
Device application	Multi-purpose
Outlet standard description	Side earth
Accessory / separate part category	Current distribution accessory
Outlet poles configuration	2P + E with shutters
Quantity per set	Set of 1
Colour	Aluminium

Complementary

Device composition	1 power rail fixing elements
Ground lug position	35° ground lug
Socket number	9
[In] rated current	16 A
[Ue] rated operational voltage	230 V AC
Mounting support	Upright 19" rack
Fixing mode	Direct fixing By brackets
Material	Polyamide 6 with 30 % fibre glass
Surface finish	Anodized
Electrical connection	3 M power cord 3 x 1.5 mm ² H05VV-F3G1.5
Number of rack unit	1U
Height	44.45 Mm
Width	Total: 482.6 mm Body: 440 mm
Depth	76 Mm

Environment

Fire resistance	850 °C
Quality labels	VDE
Standards	DIN 49440 UNE 20315 VDE 0620-1 IEC 60884

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.500 Cm
Package 1 Width	9.000 Cm
Package 1 Length	52.000 Cm
Package 1 Weight	1.080 Kg
Unit Type of Package 2	PAM
Number of Units in Package 2	200
Package 2 Height	140.000 Cm
Package 2 Width	100.000 Cm
Package 2 Length	120.000 Cm
Package 2 Weight	220.000 Kg

Offer Sustainability

RECh free of SVHC	Yes
Mercury free	Yes
RoHS exemption information	 Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant
End of life manual availability	No need of specific recycling operations
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins