

Features

- 1 Gang
- 3 Pole
- Fan Isolation
- Urea Mouldings
- White
- Stylish smooth profile plate

RS PRO Plate Switches

RS Stock No.: 0845492



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- Fits standard 25mm 1 gang back boxes
- Suitable for domestic and light commercial installations.
- Suitable for use with extractor fans

General Specifications

Plate Dimensions (mm)	86 (W) x 86 (H) x 9.5 (D)
Plate Fixing Centres (mm)	60.3
Style	Rounded Profile
Anti Microbial Certified	Yes
Product Marking	Isolator, On, Off
Warranty (Years)	25

Mechanical Specifications

Termination Type	Screw
Terminal Size (mm)	Ø3.5
Terminal Torque Value (Nm)	0.5
Terminal Capacity - Solid (mm²)	4 x 1.5 or 2 x 2.5
Minimum Back Box Depth (mm)	16
Triple Pole Switch	Yes
Ingress Protection	IP20
Operational Temperature (°C)	-5 to +40

Electrical Specifications

Frequency (Hz)	50
Resistive Load Rating (A)	10

Approvals

Standards Met	BS EN 60669-2-4, BS EN 60669-1
---------------	--------------------------------