



## FEATURES & BENEFITS

- Easy release - when the TRULOCK is disengaged the squeeze to release lever is simple to operate
- Eyebolts for higher torque tightening and faster winding
- Firm grip - optimised jaw and tooth geometry design delivers outstanding grip performance
- High performance steel protected by a striking rust resistant black finish
- Induction hardened CR-V Jaws for long-life service and reduced tooth wear
- More leverage, more tightening leverage, comfortable to use
- New rust resistant black finish on high-performance steel for a longer life
- Security - no accidental release due to TRULOCK
- Complete and consistent range for all application

SKU	Cutting capacity 100kg/mm <sup>2</sup> (mm)	Jaw Type
FMHT0-74892	280	C - Clamp Swivel
FMHT0-75408	150	C - Clamp Swivel