

Single- LED

10-
2H13.3166Q

Distribution by
Rs-online



<https://rs-online.eao.com/p/10-2H13.3166Q>

Your product:



10-2H13.3166Q Single-LED

OPERATING-/INDICATION PART

Illumination colour: Blue

ELECTRICAL CHARACTERISTICS

Operating voltage: 24 / 30 V DC +10%

Operation current: 12 - 18 mA $\pm$ 15 %

Lumi. Intensity: 560 - 800 mcd

MECHANICAL CHARACTERISTIC

Weight: 0.002 kg

CERTIFICATE

REACH: REACH compliant

RoHS: RoHS compliant


OTHER

Short Description: Single-LED, BA9s, Blue, 24 / 30 V DC +10%


Kind of illumination: Single-LED

Hints: Luminosity and wave length variations caused by LED manufacturing processes may cause slight differences regarding the illumination. The customer has to decide what resistor shall be used to the LED. Electrical and optical data are measured at 25 °C. The specified 12, 24, 28, 48 VAC/DC versions are built with a bridge rectifier

Wiring diagrams:



Dimension drawings:



A = (standard)
B = (super bright)