



Datasheet

ENGLISH

Twin Low Profile Foot Switch

RS Stock No. 116-912



Degree of protection	IP20
Materials of Construction	Sheet steel.
Colour	Black.
Cable Connection	2.5M of 16/4 cable no plug
Contact Action	SPDT Momentary wired N/O on each side
Electrical Rating	13A 125-250V a.c. 0.375kW 125-250V a.c.
Features & Benefits	Divider bar between treadles reduces accidental operation of both units. 2 holes for mounting on floor or equipment. Non skid base pad.
Weight	1.8kg
Size	(See below)

