

FEATURES

- Opal white diffuser
- Polycarbonate grey base
- Mounting hardware supplied
- Cable gland fitted to one end but with no power cord

RS PRO 40 W LED Ceiling Light, 100 → 277 V ac Batten LED NCF, 1 Lamp, 1.5 m Long, IP65

RS Stock No.: 176-8551



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO LED 40W luminaire light fitting has a high lumen output making them ideal for industrial and commercial applications such as warehouses, car parks and arenas. With an ultra-durable Polycarbonate body and diffuser and aluminium tray, they are extremely light and offer even light distribution. They come pre-fitted with stainless steel 304 clips making them an ideal fitting for food preparation areas with an operating temperature range of -25°C to +50°C.

General Specifications

Type	LED NCF
Number Of Lamps	1
Colour Tone	Daylight
Lamp Type	LED
Colour Temperature	6300K
Colour Reference	70
Anti-Corrosive	No
PIR Included	No
Applications	Ceiling lights are a very common type of light fixture which can be fitted to the ceiling in: Industrial areas; Multi-storey car parks; Workshops, warehouses and factories; Garages
Dimmable	No

Electrical Specifications

Wattage	40W
Voltage Rating	100V to 277V

Mechanical Specifications

Length	1.5m
Width	94mm
Beam Angle	120°
Lumen Output	4000lm
Ra	>70
Lumen Efficiency	100Lm/W

Protection Category

IP Rating	IP65
IK Rating	IK08

Approvals

Compliance/Certifications	RoHS Certificate Of Compliance
----------------------------------	--------------------------------



