

LEDLENSER H14R.2

This professional rechargeable head lamp takes personal lighting to new levels with its sensational performance and clever fastening system which also allows it to function as a mobile spot light, body lamp or belt torch. Boasting up to 1000 lumens of a light it is one of the most powerful and technologically-advanced head torches in the Ledlenser line up. Using a cutting edge CREE Xtreme LED Light Chip, in conjunction with Ledlenser's patented Advanced Focus System, this superb head lamp zooms out sharply-focused white light up to 300m when focused to spot beam. A simple turn of the head to refocus and a flawless flood beam for near illumination is perfectly achieved. Inside a clever pre-programmed micro-chip brings the brilliance of Smart Light Technology (SLT) to the wearer. Easily controllable from the newly designed multi-function wheel switch on the battery pack, SLT gives the user two energy usage modes (Constant Current, Energy Saving), three light programmes (Easy Low, Easy Power, Signal) and six light options (Power, Low Power, Boost, Blink, Dim, Pulse). It means that no matter where you are there's a light function to get you into action or even out of trouble. A rear safety light has red or blinking light options so that your colleagues are always aware of your location and a Low Battery Message System informs when the batteries need charging which can be done from the supplied mains or USB charging connectors. An eco-friendly Transport Lock prevents the light from being switched on by accident so draining the battery unnecessarily. Weight: 340g. Burn time: 35 hours. Supplied with: Li-ion Battery Pack, Belt Hook, Mains Charger, USB Cable, User Manual.

As a leading international brand of hand-held torches and head lamps, Ledlenser is renowned for superior German engineering, outstanding performance, and state-of-the art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class-leading lighting instruments, Ledlenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. Ledlenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability that is second to none.

- A 3-in-1 rechargeable head lamp that cleverly also transforms into a mini spotlight or belt/body lamp
- Energy efficient CREE Xtreme LED Light Chip
- State-of-the-art, reliable German engineering
- Advanced Focus System™ Optics. Patented reflector and lens combination for intense spot (distance) or flawless flood (near) illumination
- Smart Light Technology(SLT). Micro-chip controlled multi-option technology featuring two energy usage modes (Constant Current, Energy Saving), three pre-set light programs utilising six light options (Power, Low Power, Boost, Blink, Dim, Pulse)
- Multi-function Dynamic 'wheel' switch. Controls SLT options , Dim option and light intensity of Power, Low Power and Boost options which can be adjusted to as low as 5 lumens. Also controls the flashing rate of Signal option (from Blink to Strobe)
- Directional light. Lamp head pivots within 90° angle.
- Robust cabling. Areas exposed to strain toughened and more flexible
- Low Battery Message System. Light blinks 3 times every 15 seconds to indicate low battery
- Battery Life Indicator. Shows battery life remaining when first switched on.
- Transport lock. Prevents the light from being switched on by accident and draining battery
- Ergonomic comfort design.
- Recalibrated lens for wider light beam angle
- Corrosion resistant gold plated contacts for better conductivity
- Water and dust resistant. IPX4

Technical Information

H14R.2	BOOST	POWER	LOW POWER
POWER	1000 lumens	450 lumens	60 lumens
BEAM DISTANCE	300 metres	200 metres	70 metres
RUN TIME	6 hours	12 hours	35 hours
SIZE	x	WEIGHT	340g

Supplied with : Belt Hook and Lithium-Ion Battery Pack



Code	Packaging	Barcode
7299R	Box	4029113729932

RRP ex.vat £128.29 / incl.vat £153.95

RRP ex.vat €137.76 / incl.vat €169.45