

MPO Loopback Plug, Single Mode 9/125 MPO-12 Male Fiber Loopback Adapter, MPO/MTP-APC Connector Loopback Test Plug, MPO Male Loopback Tester

Product ID: LOOPBACKMTP12OS2SMM



This Single Mode MPO Loopback Plug is a practical tool for verifying signal continuity, insertion loss, and port function in fiber optic networks. Ideal for technicians and IT Pros, it enables fast, consistent testing across MPO-based fiber connections.

This 9/125um MPO-12 Loopback Adapter is compatible with OS1 and OS2 cabling in point-to-point and structured installations. IEC and RoHS compliance ensures readiness for standardized deployments and testing in regulated environments.

Validate MPO transceivers, isolate faults, and confirm port behavior across high-speed parallel optic links. The fixed 12-fiber configuration with precision-aligned ferrules deliver clean signaling for accurate, reliable diagnostics.

The MPO-12 male connector attaches directly to female MPO/MTP ports for high-density testing without disrupting adjacent connections. A durable ABS housing withstands wear from repeated use and is suitable for frequent testing in data centers and edge or on-prem installations.

Certifications, Reports and Compatibility



Applications

Features

- **Reliable Fiber Testing**: Create a loopback test connection with this MPO Single Mode fiber loopback plug; Male MPO-12 connector for testing female MPO/MTP ports; Test 12-fiber MPO installations and QSFP transceivers for continuity
- **Accurate Test Performance**: Maintain precise loopback signaling with insertion loss below 0.35dB; Repeatability within 0.2dB ensures consistent results across multiple connections; Return loss above 50dB minimizes back-reflection for stable signaling
- **Built for Durability**: Optimized for multiple test cycles using high-precision ceramic ferrules in a compact ABS housing; Built in compliance with IEC and RoHS standards for reliable testing in regulated environments
- **Field-Ready Design**: Compact form factor is ideal for technicians performing on-site diagnostics and fault isolation; Quickly troubleshoot cables and verify performance in single mode MPO/MTP patch panels and transceivers; Includes protective dust cap
- **The IT Pro's Choice**: Our network tools and testers are rigorously tested in our Innovation Lab to ensure enterprise-grade reliability and durability; Built for quick diagnostics and routine maintenance across copper and fiber networks; Backed by free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	1 Year
Fiber Size	9/125
Fiber Classification	OS2
Industry Standards	IEC 6175420

Performance

Insertion Rating	Rated for 1,000 testing cycles
------------------	--------------------------------

Environmental

Operating Temperature	-40C - 75C (-40F to 167F)
Storage Temperature	-40C - 75C (-40F to 167F)
Humidity	N/A

Physical Characteristics

Color	Black & Green
Material	ABS
Product Length	5.1 in [130 mm]
Product Width	0.5 in [11.8 mm]
Product Height	0.4 in [9.4 mm]

	Weight of Product	0.1 oz [4 g]
Packaging Information		
	Package Length	4.7 in [12.0 cm]
	Package Width	8.7 in [22.0 cm]
	Package Height	0.5 in [1.3 cm]
	Shipping (Package) Weight	0.3 oz [9.0 g]
What's in the Box		
	Included in Package	1 - MTP/MPO Fiber Loopback Plug - Male

****Product appearance and specifications are subject to change without notice.***