

Specifications



Photo is representative

Eaton FAZ-C40/1-NA

Eaton FAZ branch protector,UL 489 Industrial miniature circuit breaker - supplementary protector,Medium levels of inrush current are expected,40 A,10 kAIC, 14 kAIC,Single-pole,277/480 V,5-10X/n,50-60 Hz,Screw terminals,C Curve,Supplementary

General specifications

PRODUCT NAME	Eaton FAZ branch protector
CATALOG NUMBER	FAZ-C40/1-NA
EAN	4015081019724
PRODUCT LENGTH/DEPTH	1.5 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.57 lb
CERTIFICATIONS	UL 489
CATALOG NOTES	Positioned for medium inrush startup currents to provide protection for small transformers and pilot devices.



Powering Business Worldwide

Physical Attributes

NUMBER OF POLES	Single-pole
TERMINALS	Screw
TYPE	UL 489 Industrial miniature circuit breaker - supplementary protector

Miscellaneous

APPLICATION	Suitable for applications where medium levels of inrush current are expected
--------------------	--

Performance Ratings

AMPERAGE RATING	40 A
CIRCUIT PROTECTION	C curve
FREQUENCY RATING	50-60 Hz
INTERRUPT RATING	14 kAIC 10 kAIC
TRIP TYPE	5-10X /n
VOLTAGE RATING	277/480V

Resources

CATALOGS	UL 489 DIN rail miniature circuit breakers
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - FAZ-C40/1-NA

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

