



ENGLISH

Datasheet

Trailing Socket 4 NF +USB 1.5m switched



31/07/2017

RS Stock Number:**Specifications:**

Electrical Rating	16A 250V
Dielectric Strength	1000VAC for 1 min between current carrying parts 2500VAC for 1 min between non-current carrying parts
Operating Temperature	-20 ~ +80°C (-4 ~ 176°F)
Degree of Protection	IP20/NEMA 1

Features:

- **NF/CE Certified**
- **Trailing Socket 4 NF +USB 1.5m switched**
- **1.5meter, H05VV-F, 3G1.5MM cable**