

M18 FN18GS-0X

M18 FUEL™ 18 GS FINISH NAILER

- Excellent power to consistently seat nails sub-flush to the surface in hardwoods
- Ready to Fire Nail Technology eliminates ramp-up time between each nail discharge
- No gas cartridges and no cleaning required, designed to deliver durability and reliability to the most demanding users with very little maintenance
- Smaller nail hole, the exact size of the nail head leaving a neater finish
- Different shaped noses stored on board allows the user to get the best finish no matter what the application
- Small work contact bracket allows the user to fire and sink nails at a more acute angle
- Tool-free, quick and easy depth adjustment to assure nails are driven sub-flush
- Dry-Fire lockout stops the tool being fired when there are no nails left in the magazine
- Fires up to 1200 nails per charge on a REDLITHIUM™ 2.0 Ah battery pack for maximum productivity
- Quick access and easy clearing of jams
- LED work light illuminates the work surface for better placement of nails
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™

Collation angle [degrees]	0
Nail diameter [mm]	1.2
Nail type (mm)	16 / 54
Magazine capacity nails	110
Cycle rate	900
Kit included	No batteries supplied, No charger supplied, HD Box
Article Number	4933471409

