



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

| LOC | DIST | REVISIONS | | | |
|-----|------|-------------|--------------|---------|-------|
| P | LTR | DESCRIPTION | DATE | DWN | APVD |
| BD | 39 | G | 0G3B-0317-03 | 24APR03 | TK GS |



ACCOMODATES
1.57 DIA PIN
[.062]



LOCALIZED TIN-LEAD,
OR TIN, PLATE AREA

1. WIRE RANGE 18-16 AWG.
2. INSULATION RANGE 2.03-2.54 [.080-.100] DIA.
3. 0.76µm [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA,
1.27µm [.000050] MIN TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA,
BOTH OVER 1.27µm [.000050] MIN NICKEL.
4. TIN PLATED.
5. GOLD PLATING PER MIL-G-45204, TIN PER MIL-T-10727
AND NICKEL PER QQ-N-290.
6. 0.76µm [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA,
1.27µm [.000050] MIN TIN IN LOCALIZED TIN PLATE AREA,
BOTH OVER 1.27µm [.000050] MIN NICKEL.

| STRIP REF | FINISH | PART NO |
|-----------|--------|---------|
| 66580-7 | 6 | 66590-4 |
| 66580-4 | 3 | 66590-2 |
| 66580-2 | 4 | 66590-1 |

| | | | | |
|---|--|----------------------------------|---|-----------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN D.HARDY 06/15/94 | Tyco Electronics Corporation Harrisburg, Pa | |
| DIMENSIONS: INCHES | | CHK R.STONE 06/22/94 | NAME CONTACT, SOCKET, LOOSE PIECE, TYPE VI, MULTIMATE | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: | | APVD G.STEINHAUER 06/27/94 | PRODUCT SPEC - | RESTRICTED TO - |
| MATERIAL BRS PER MIL-C-50 | | FINISH 5 SEE TABLE | APPLICATION SPEC - | SIZE A3 |
| | | WEIGHT - | CAGE CODE 00779 | DRAWING NO C-66590 |
| CUSTOMER DRAWING | | | SCALE 6:1 | SHEET 1 OF 1 |
| | | | REV G | |