



iM2275

Storm

Give your gear extra space. With a deeper lid, the iM2275 is the first case in our Peli™ Storm Case™ line that gives you more vertical space to work with for your equipment. This case gives you the freedom to configure multiple 4K cameras, diagnostic circuit readers, or a drone with accessories.

- **Watertight, crushproof, and dustproof**

- Two Press & Pull Latches
- Two Padlockable Hasps
- Double-layered, Soft-grip Handle
- Vortex™ Valve
- Powerful Hinges
- Lightweight Strong HPX® Resin



CONFIGURATIONS



iM2275
Standard



iM2275-X0000
No Foam



iM2275-X0006
With TrekPak Divider System



iM2275-X0001
With Foam

DIMENSIONS

Interior (L×W×D)	14.12 x 13.19" x 9.90 (35.9 x 33.5 x 25.1 cm)
Exterior (L×W×D)	15.25 x 15.50" x 10.22 (38.7 x 39.4 x 26 cm)
Lid Depth	3.20" (8.1 cm)
Bottom Depth	6.30" (16 cm)
Total Depth	9.5" (24.1 cm)
Int Volume	1.07 ft ³ (0.03 m ³)
Padlock Hole Diameter	0.37" (0.9 cm)

MATERIALS

Body	Injection Molded HPX™ high performance resin
Latch	Valox - Polybutylene Terephthalate (PBT)
Latch (Alt)	Xenoy - Polyester/Polycarbonate blend
O-Ring	EPDM
Pins	Stainless Steel
Pins (Alt)	Aluminum
Foam	1.3/1.35 polyester
Purge Body	Valox - Polybutylene Terephthalate (PBT)
Purge Body (Alt)	Xenoy - Polyester/Polycarbonate blend
Purge Vent	Gortex membrane

COLOURS

■ Black

WEIGHT

Weight With Foam	10.25 lbs (4.6 kg)
Weight Empty	8.00 lbs (3.6 kg)
Buoyancy	68.80 lbs (31.2 kg)

TEMPERATURE

Minimum Temperature	-20°F (-28.9 °C)
Maximum Temperature	140°F (60 °C)

CERTIFICATIONS

IP67

OTHER

Master Pack	3
Military	yes

ACCESSORIES



iM-STRAP-S-VER2
Padded Shoulder Strap



iM-LIDSTAY
Lid Stay



iM2275-FOAM
4 pc. Replacement Foam Set



1506TSA
TSA Lock



1500D
Desiccant Silica Gel



IM2275TPDIV
Extra TrekPak Dividers