

## Features

- PVC Coated Lacing Cord
- 500M designed for the lacing of cable forms.
- Nylon core ensures high tensile strength
- Wide temperature range.
- PVC sheath acts as a cushion preventing the cord from cutting into the cable insulation.
- Includes a maximum limit on tensile strength to prevent excessive tension in lacing

## RS PRO Orange Lacing Cord - 1mm diameter

RS Stock No.: 0665321



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

*High-quality lacing rope used for professional cable management. Lacing cord made from Nylon with a PVC coating which is strong enough for traditional lacing techniques such as square lashing and clove hitch. Used in telecommunication applications to create aesthetically pleasing or clean functional installations.*

## General Specifications

Length	500M
Colour	Orange
Thickness	1mm (0.040")
Material	Nylon Core, PVC Coated

## Mechanical Specifications

<b>Elongation Percentage</b>	5%
<b>UV Resistance</b>	Pass UL - 1581 720h Sunlight
<b>Cold Flex Tolerance</b>	-54°C UL - 1581 Cold Bend
<b>Maximum Service Temperature</b>	138°C 168 Hours Continuous Exposure
<b>Brittleness Temperature</b>	-15°C A.S.T.M. D - 746
<b>Flame Resistance: Pass M</b>	VSS 302, SAEJ369, & UL94 V0 @ 125 mils
<b>RoHS, Reach, ELV</b>	Yes
<b>Tensile Strength lbs</b>	22.0 (9.97Kg)

## Electrical Specifications

--	--

## Protection Category

Non-Metallic Metals	
---------------------	--

## Classification

eCl@ss (Version)	
UNSPSC (Version)	

## Approvals

Declarations	MFR Declaration of Conformity
Hazardous Area Certification	
Standards Met	

## Similar Products

Stock No.	Brand	Product Name	Attribute 1	Attribute 2	Attribute 3
	RS PRO				
	RS PRO				

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories