



**ENGINEERED IN
GERMANY**



Product number 1150660325
EAN 4007123656752

DESCRIPTION

- Elegant design.
- Sockets arranged at a 90° angle.
- Ideally suited for connecting angled plugs.
- Wide socket outlet spacing enables the operation of power supply units.
- Illuminated safety switch, can be switched on/off with two poles.
- Optimum mounting option thanks to screw holes for easy fixed mounting of the socket strip, e.g. on the wall.
- Charging of your connected devices thanks to two integrated USB A ports 5 V/2.10 A, 10.5 W.
- Sockets with increased contact protection.

TECHNICAL DATA

Cable quality	PVC	Max. current carrying capacity	16 A
Cable length	3 m	USB charging units	2x /Technische Attribute/Anschlussbuchse/Typ A
Cable designation	H05VV-F 3G1,5	Max. output current USB	2.1 A
Socket outlets total	5	Output socket type A	2
Plug system plug	Type E and F (Protective contact with earth hole)	Colour	white
Circuit breaker	No		

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	0.67 kg
Weight of product (without packaging)	0.66 kg	Dimension LxWxH (incl. packing)	8.5 cm x 7 cm x 46.5 cm
Dimension LxWxH (without packing)	8 cm x 7 cm x 43 cm		

SCOPE OF DELIVERY

Bremounta extension lead