

FEATURES

- Lockable protection window on all variants to enhance safety
- IP44 Rated, 0410185 is IP66 rated
- Wall mountable
- Red and blue colours offered in this range of power connectors
- Voltage ratings of 415V and 230V offered in this range
- Angled socket, allowing a more convenient connection
- All models offered in the range are highly reliable and excellent quality

IP44 Red Wall Mount 3P+E RCD Industrial Power Connector Socket, Rated At 16.0A, 415.0 V

RS Stock No.: 410-084



Product Description

It comes a range of high-quality wall mountable power connectors. Manufactured to industry standards these connectors are easy to assemble and are a fantastic industrial plug solution for powering tools and machinery at a range of different voltage requirements.

General Specifications

Version	With protection appliance
Commercial Series	DOMINO Series
Pole Format	3P+E
Gender	Female
Body Orientation	Angled
Material	Engineering Plastic
Colour	Red
Applications	Providing power for machinery on construction sites, Woodworking machines, Maintenance workshops in the light industry

Electrical Specifications

Type of Current	AC
Current Rating	16A
Voltage Rating	415V
Working Frequency	50Hz; 60Hz
Plug/Socket	Socket
Termination Method	Pre-Wired
RCD Protection	Main switch with RCD

Mechanical Specifications

Mounting Type	Wall Mount
----------------------	------------

Industrial Power Connectors

Protection Category

IP Rating	IP44
-----------	------

Approvals

Compliance/Certifications	EN61340
---------------------------	---------

