

Datasheet

Thin HDMI Cable

- 9134843
- 9134846
- 9134840
- 9134859
- 9134852
- 9134856
- 9134865
- 9134868
- 9134862
- 9134871
- 9134874
- 9134878
- 9134887
- 9134880



A braided aluminium HDMI cable with a robust aluminium head shell for high levels of reliability & abrasion protection.

- Triple shielded
- Full 3D support
- Supports Audio Return Channel
- High Speed Ethernet
- Excellent conductivity due to oxygen free conductors



18/12/2015



Professionally approved products.
Datasheet

Thin HDMI Cable

- 9134843
- 9134846
- 9134840
- 9134859
- 9134852
- 9134856
- 9134865
- 9134868
- 9134862
- 9134871
- 9134874
- 9134878
- 9134887
- 9134880



ECN MARK	ECN NO.	DESCRIPTION	DATE
			2013/09/23



**5P+4C(30AWG)
1.4 Version**

FEATURES

- 1. Gold-plated plugs
- 2. compliant ROHS. 1080P

ELECTRICAL SPECIFICATION:

- 1. Withstanding voltage: 300VDC 0.1SEC
- 2. Insulation Resistance: 5Mohm 300VDC

LENGTH
7500mm
6000mm
5000mm
4000mm
3000mm
2000mm
1500mm
1000mm
500mm

Type A PIN	Signal Assignment	Type A PIN
1 Blue	Blue 1	Blue 1
2 ground	ground 2	ground 2
3 white	white 3	white 3
4 Blue	Blue 4	Blue 4
5 ground	ground 5	ground 5
6 white	white 6	white 6
7 Blue	Blue 7	Blue 7
8 ground	ground 8	ground 8
9 white	white 9	white 9
10 Blue	Blue 10	Blue 10
11 ground	ground 11	ground 11
12 white	white 12	white 12
14 Blue	Blue 14	Blue 14
17 ground	ground 17	ground 17
19 white	white 19	white 19
15 Yellow	Yellow 15	Yellow 15
16 Orange	Orange 16	Orange 16
13 white	white 13	white 13
18 red	red 18	red 18
SHELL	SHELL	SHELL

ITEM.	DESCRIPTIONS&SPECIFICATIONS	QTY	REMARK
1	HDMI Type A Plug 19Pin(Pins Gold-Plated,Shell Gold-Plated)	2PCS	
2	AL Metal Shell(Colors: green, blue, red)	2PCS	
3	PVC 60P Black		
4	30AWG OD:6.0 Black PVC Jacket		

TOLERANCE	SIGNATURES	DATE	SCALE	TITLE
20-99 ±20.00 100-999 ±30.00 1000-9999 ±50.00 10000-99999 ±100.00	DRAFT: <i>neo</i> CHECKED: <i>samo</i> APPROVAL: <i>zing</i>	2013		4
Unit:MM	REV	A1	DWG 1/0	

18/12/2015