

Specifications

Photo is representative

Eaton 7.2WFNHA80

Motor fuse-link, medium voltage, 80 A, AC 7.2 kV, 76 x 403 mm, back-up, BS, with striker, no tags HS

General specifications

PRODUCT NAME	Eaton Bussmann series medium voltage motor fuse
CATALOG NUMBER	7.2WFNHA80
MODEL CODE	7.2KV 80A 3" MOTOR START FUSE
EAN	5027590488617
PRODUCT LENGTH/DEPTH	403 mm
PRODUCT HEIGHT	76 mm
PRODUCT WIDTH	76 mm
PRODUCT WEIGHT	4400 g
COMPLIANCES	BS 2692-1
PRODUCT TYPE	Medium voltage motor fuse



Powering Business Worldwide

Electrical Ratings

AMPERAGE RATING	80 A
INTERRUPT RATING	40 kAIC
VOLTAGE RATING	7.2 kV

Physical Details

PACKAGING TYPE	Standard
TYPE	fuse

General Information

APPLICATION	Motor protection
CLASS	Class back-up
CONSTRUCTION SIZE	76 x 403 mm
FUSE TYPE	WFNH
USED WITH	A3354730 Nickel-plated copper fuse clip

Resources

BROCHURES	eaton-bussmann-circuit-protection-brochures-en.pdf
-----------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

