

182.72.104.66ZL2..-DRSZapfenlaufrollen

Stud type track rollers ZL205-DRS (Series ZL2..-DRS)

lip seal on one side

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

D	62 mm
d1	25 mm
B	33,8 mm
B1	18 mm
max	
B2	16 mm
B4	31 mm
C	15 mm
C1	2 mm
d2	30,3 mm
g	M10
lg	19 mm
R	500 mm Crowning radius
rmin	1 mm
m	0,25 kg Mass
Cr	13300 N Effective dynamic load rating as track roller (radial)
w	
C0r	7100 N Effective static load rating as track roller (radial)
w	
Cur	360 N Fatigue limit load
w	
nd	5500 1/min Speed (with continuous operation and grease lubrication)
G	

