



Main

Range of product	KNX
Product or component type	Binary input
Bus type	KNX

Complementary

Total number of 18 mm modules	2.5
Wiring device mounting	DIN rail
[Ue] rated operational voltage	24 V AC/DC 50 Hz
Number of inputs	4
Input type	Binary
Local signalling	LED

Environment

IP degree of protection	IP20
-------------------------	------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins