

222025000

Polyester Enclosure Cabinet
200 x 250 x 150 mm

Polyester Enclosure Cabinet 200 x 250 x 150 mm

Catalogues | Declaration of Conformity | Drawing | 3D Data

Technical data

Height	200 mm
Width	250 mm
Depth	150 mm
Material	Polyester
Colour	Pebble grey (RAL 7032)
Ingress protection	IP65
Degree of protection norm	EN 60529
Impact strength	IK09
temperature min.	-30 °C
temperature max.	90 °C
Insulation	Fully insulated according to VDE 0100
Toxicity	Halogen free
Surface resistance	4x10^15 Ohm
Surface resistance norm	IEC 60093
Special colours on request	Yes

Commercial data

Order unit	1 Piece
Customs tarif number	39269097
Weight	1.08 kg
GTIN	4250157915696


ETIM classification

ETIM 8	EC000261


ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories



100112050
Mounting plate for 21.202500



100131010
Front plate for 21.202500

Zubehör - s. Zeichnung
Accessories - see drawing

216200010
Standard handle for Polyester cabinets

Zubehör - s. Zeichnung
Accessories - see drawing

216200020
Standard handle with lock for Polyester cabinets

Zubehör - s. Zeichnung
Accessories - see drawing

216200030
Triangular lock for Polyester cabinets

Zubehör - s. Zeichnung
Accessories - see drawing

216200040
Square lock for Polyglas (8mm)