

Motorcbl. Q8/0 M 4G1.5 3.0m



Image is for illustration purposes only. Please refer to product description.

Part number	61 88 201 0212 00
Specification	Motorcbl. Q8/0 M 4G1.5 3.0m
HARTING eCatalogue	https://harting.com/6188201021200

Identification

Element	Motor cable
Specification	Pre-assembled on one side
Connector 1	Han-Compact® Hood Han® Q 4/2 Male
Type of cable	Copper cable (round)

Version

Cable length	3 m
Core structure	4x 1.5 mm ²
PE contact	Yes
Field of application	for motor connection

Material properties

Material (cable)	PVC
Colour (cable)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
ECHA SCIP number	ae0bdeb2-a56c-4d51-aeb1-e094fa9de4c4



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Commercial data

Packaging size	2
Net weight	386.6 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140274280
eCl@ss	27060490 Ready-made low-voltage line (unspecified)
ETIM	EC002587
UNSPSC 24.0	26121629