



verso adjustable height storage bench with full cupboard / 3 drawer cabinet. Featuring a robust, steel channel, adjustable height framework with integrated storage units and a 30mm multiplex wood worktop. Delivered assembled. Integrated cabinet sizes -WxDxH: 525+800x550x600mm. Drawer configuration: 1x 125mm, 2x 175mm with 100% extension slides (75kg U.D.L.) and a single reinforced door. Finished in durable powder coat paint in RAL 7035 light grey / RAL 3004 crimson red. WxDxH: 1500x600x830-930mm.

Breite [mm]: 1500
Tiefe [mm]: 600
Höhe [mm]: 930
Bruttogewicht [kg]: 112.34
EAN-Code: 5039350102411
Zolltarifnummer UK: 94032080
Ursprungsland: GB

Produkteigenschaften

Product surface	Powder coated
Product material	Sheet steel
Main colour	Crimson red
Main RAL colour	RAL 3004
Secondary colour	Light grey
Secondary RAL colour	RAL 7035

Artikelbeschreibungen

Product brand	verso
---------------	-------

Schubladen

Number of drawers	3
Drawer load capacity [kg]	75
Drawer height 1 [mm]	125
Drawer height 2 [mm]	175
Drawer height 3 [mm]	175

Schrank, Gehäuse, Werkbank und EAP

Height adjustment range [mm]	830-930
Worktop/housing top type	Beech Multiplex
Door type	Plain
Door height 1 [mm]	475