

20 ft DVI-I Dual Link Digital Analog Monitor Cable M/M

Product ID: DVIIDMM20



The DVIIDMM20 DVI-I Dual Link cable features 2 male DVI-I (29-pin) connectors and offers 20 feet in cable length, making it perfect for longer connections between your desktop or laptop computer and a DVI-I monitor or projector.

The 20ft DVI-I male to male cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Connect your desktop or laptop computer to a DVI-I Dual Link display or projector

Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards
- Supports both analog and digital displays

	Warranty	Lifetime
Hardware	Industry Standards	DVI DDWG Standard
Performance	Maximum Data Transfer Rate	9.9 Gbits/sec
Connector(s)	Connector A	1 - DVI-I (29 pin) Male
	Connector B	1 - DVI-I (29 pin) Male
Physical Characteristics	Cable Length	6.1 m [20 ft]
	Color	Black
	Product Length	6.1 m [20 ft]
	Weight of Product	757 g [26.7 oz]
	Wire Gauge	28/30 AWG
Packaging Information	Package Height	50 mm [2 in]
	Package Length	33 cm [13 in]
	Package Width	25.5 cm [10 in]
	Shipping (Package) Weight	774 g [27.3 oz]
What's in the Box	Included in Package	1 - 20 ft Dual Link Digital Analog Monitor DVI-I Cable - M/M

Product appearance and specifications are subject to change without notice.