



Brute lids



FG263100GRAY



FG261960BLA

FG260900, FG263100, FG265400 Snap-on lids

- All-plastic, professional-grade construction will not rust, chip or peel; resists dents.
- Strong, snap-on lids are available for secure, stable stacking.
- Built-in handles allow easy, non-slip lifting and anti-jam nesting.
- Gray, White and Yellow are USDA Meat & Poultry Equipment Group Listed and assist in complying with HACCP guidelines.

FG261960, FG264560 Brute lids

- Self-draining lid reduces pooling when containers are stored outside.

PRODUCT INFORMATION

Ref.	Description	Material	Product Dimensions (cm)	Colour	Pack
FG260900GRAY	Snap-on Lid (fits FG261000)	Polyethylene	ø 40.6 x 2.5 cm	Gray	6
FG260900WHT	Snap-on Lid (fits FG261000)	Polyethylene	ø 40.6 x 2.5 cm	White	6
FG261960BLA	BRUTE® Lid (fits FG262000)	Polyethylene	ø 50.5 x 4.6 cm	Black	6
FG261960DGRN	BRUTE® Lid (fits FG262000)	Polyethylene	ø 50.5 x 4.6 cm	Green	6
FG261960GRAY	BRUTE® Lid (fits FG262000)	Polyethylene	ø 50.5 x 4.6 cm	Gray	6
FG261960WHT	BRUTE® Lid (fits FG262000)	Polyethylene	ø 50.5 x 4.6 cm	White	6
FG261960YEL	BRUTE® Lid (fits FG262000)	Polyethylene	ø 50.5 x 4.6 cm	Yellow	6
FG263100DGRN	Snap-on Lid (fits FG2632)	Polyethylene	ø 56.5 x 3.5 cm	Green	6
FG263100GRAY	Snap-on Lid (fits FG2632)	Polyethylene	ø 56.5 x 3.5 cm	Gray	6
FG263100RED	Snap-on Lid (fits FG2632)	Polyethylene	ø 56.5 x 3.5 cm	Red	6
FG263100WHT	Snap-on Lid (fits FG2632)	Polyethylene	ø 56.5 x 3.5 cm	White	6
FG263100YEL	Snap-on Lid (fits FG2632)	Polyethylene	ø 56.5 x 3.5 cm	Yellow	6
FG264560BLA	BRUTE® Lid (fits FG264300)	Polyethylene	ø 62.2 x 3.8 cm	Black	4
FG264560GRAY	BRUTE® Lid (fits FG264300)	Polyethylene	ø 62.2 x 3.8 cm	Gray	4
FG264560WHT	BRUTE® Lid (fits FG264300)	Polyethylene	ø 62.2 x 3.8 cm	White	4
FG264560YEL	BRUTE® Lid (fits FG264300)	Polyethylene	ø 62.2 x 3.8 cm	Yellow	4
FG265400GRAY	Snap-on Lid (fits FG265500)	Polyethylene	ø 67.92 x 5.1 cm	Gray	3



Brute lids

SHIPPING INFORMATION

Ref.	Country of Origin	EAN Product code	Carton Dimensions (cm)	Weight (kg)	Vol (m³)
FG260900GRAY	USA	00086876012385	43x41.5x19	2.4	0.037
FG260900WHT	USA	00086876012415	43x41.5x19	2.4	0.037
FG261960BLA	USA	00086876191752	50.8x50.8x29.5	4.2	0.064
FG261960DGRN	USA	00086876203073	50.8x50.8x29.5	4.2	0.064
FG261960GRAY	USA	00086876191714	50.8x50.8x29.5	4.2	0.064
FG261960WHT	USA	00086876191738	50.8x50.8x29.5	4.2	0.064
FG261960YEL	USA	00086876191745	50.8x50.8x29.5	4.2	0.064
FG263100DGRN	USA	00086876179040	58.5x57.8x23	6.0	0.078
FG263100GRAY	USA	00086876014655	58.5x57.8x23	6.0	0.078
FG263100RED	USA	00086876014013	58.5x57.8x23	6.0	0.078
FG263100WHT	USA	00086876014662	58.5x57.8x23	6.0	0.078
FG263100YEL	USA	00086876014051	58.5x57.8x23	6.0	0.078
FG264560BLA	USA	00086876183597	62.9x62.9x26.7	4.7	0.110
FG264560GRAY	USA	00086876187465	62.9x62.9x26.7	4.7	0.110
FG264560WHT	USA	00086876187496	62.9x62.9x26.7	4.7	0.110
FG264560YEL	USA	00086876187502	62.9x62.9x26.7	4.7	0.110
FG265400GRAY	USA	00086876016505	70.5x69.0x18.8	5.2	0.088