

S.306-100R | S.306R - CLICK WRENCHES WITH ATTACHMENT 20 X 7 MM




Norm :

NF EN ISO 6789, ISO 6789, DIN EN ISO 6789

Description :

- Factory accuracy: $\pm 2\%$.
- Reliability of mechanism: 50,000 cycles (wrenches --> 200 N.m).
- Use possible with accessories attachment 20 x 7 mm.
- One-way wrenches usable for unscrewing by reversing the bits.
- Numbered wrenches supplied with ISO 6789 calibration certificate.
- Wrenches supplied in plastic protection tube.

Informations :

	S.306-100R
L [mm]	420
Attachment	20 x 7
Capacity [N.m]	20 - 100
Graduation [N.m]	1
[kg]	1