

HyFlex[®] 11-627

General Purpose

Orig	02-03-2004
Rev	03-07-2007

Product description

Dyneema®/Lycra®/Nylon automatic knit coated with a PUR coating

Glove material

- Polyurethane coating
- Dyneema®/Lycra®/Nylon liner
- Natural rubber latex (elasticated cuff)

Sensitizers

- Natural rubber proteins
 Only a very small number of users may be sensitised to these ingredients in the glove and hence may develop irritant and/or allergic contact reactions.

Properties

- Very good cut resistance
- Superior comfort due to the no seams knitted liner
- Superior flexibility and dexterity due to the thin membrane
- Machine washable at 40°C
- Superior abrasion resistance

EN test data

Abrasion resistance : Performance level 4 (> 8000 cycles)
Blade cut resistance : Performance

level 3 (index average 6,7)

Tear resistance : Performance level 4 (> 75 N)

Puncture resistance : Performance level 2 (min. 60 N)

European conformity

Gloves conform to the requirements of the European Directive 89/686/EEC and to the European standards EN 420:2003 and EN 388:2003. They are categorised in "Intermediate Design" (= Protection against intermediate risks).
 EC-type examination by
CENTEXBEL
Technologiepark 7
B-9052 Zwijnaarde

Application-Limitations of use

Hand protection - medium duty cut risks. For detailed information, please contact Ansell; This glove is liquid repellent but not liquid proof. This glove should not be used as a chemical resistant product.
 Do not use against flames or temperatures < -25°C or > 100°C.

Storage

Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.

Type	Style	Colour	Reference	(EN) Sizes	Length
Palm coated	Elasticated cuff	Grey	11-627	6	203 mm
				7	220 mm
				8	225 mm
				9	245 mm
				10	255 mm

The length of the gloves are below the EN requirements for total minimum glove length. Hence, the glove is called 'Fit for special purpose'.

Ansell Healthcare Europe N.V. (European Head Office)

Riverside Business Park, Spey House Boulevard International 55 B-1070 Brussels, Belgium
 Tel. +32 (0) 2 528 74 00 Fax +32 (0) 2 528 74 01 Fax Customer Service +32 (0) 2 528 74 03

Ansell (UK) Limited

30-32 Mariner Lichfield Road Industrial Estate Tamworth Staffordshire B797UL, United Kingdom
 Tel. +44 1827 302100 Fax +44 1827 302101
<http://www.anselleurope.com> E-mail info@eu.ansell.com



ISO 9001 Certificate
 Number FM 40130