



Cut protection

KRYTECH 558

Low risk - ISO B



CUT PROTECTION
LEVEL B



CATEGORY 2



ISO 13997:
5.3 N

DEXTERITY

EN ISO 21420:
5/5

Standard protection for intricate handling in reasonably clean environments

SPECIFIC ADVANTAGES



Cut protection

- A long cuff for a better protection of the forearm



Comfort

- Excellent dexterity and optimized shape to reduce fatigue.



Durability

- Suitable for long-term wear : excellent abrasion resistance
- A reinforced crotch in nitrile for an improved durability for the most exposed areas



Skin protection

- Contains traces of DMF in compliance with occupational exposure limits



Washability

- Washable up to 5 times at 60°C , allowing to extend glove lifespan, reducing costs and waste.

INDUSTRIES

- Automotive/mechanical industry
- Construction Industry (Carpenters/Joiners)
- Construction Industry (Metalworkers/Locksmiths)

APPLICATIONS

- Handling and installing metal structures
- Installing steel structures
- Bodywork assembly
- Mechanical maintenance




Cut protection

KRYTECH 558

Low risk - ISO B

LEGENDS



PRODUCT DETAILS

Interior finish	Seamless textile support from HDPE fibres
Gauge	13
Material	Polyurethane
Cuff characteristic	Long cuff
Colour.s	Grey
European sizes	6 7 8 9 10 11

LOGISTIC DETAILS

Packaging	1 pair/bag 12 pairs/bag 96 pairs/carton
-----------	---

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/02/0612 - EXT 01/02/19
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE