

HyFlex®

ADVANCED MECHANICAL PROTECTION

11528

Skin friendly cut protection with
INTERCEPT technology®



Cut



Light Duty

Highly durable light-duty work gloves, ensuring comfort, flexibility and grip

- **Improved durability:** HyFlex® 11-528 light-duty industrial gloves' NBR foam coating ensures heightened durability and meets EN ABRASION LEVEL 3
- **Enhanced grip:** Their NBR foam coating also enhances these safety gloves' grip performance for dry to moderately oily applications
- **Assured protection:** Featuring glass-free INTERCEPT™ Cut Resistance Technology, that ensures EN ISO B level cut resistance
- **Heightened tactility:** These HyFlex® gloves are also highly flexible, providing the ideal range of motion and tactility needed for handling small parts
- **Minimized health risks:** DMF-free by design, they avoid all related health risks



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Mining
- Oil and gas
- Transportation

Applications

- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Final assembly
- Assembly & inspection of components
- Applying finish to materials, products

Key Features

- **Glass-free INTERCEPT™ liner:** Enhanced cut protection
- **NBR foam coating:** Strong grip and advanced abrasion resistance
- **Flexible design:** Ample range of motion and tactility

Vulcanization Chemical Accelerators

- Natural rubber proteins (in knitwrist elastic)

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Technologies



Fibre glass free



Performance Standards & Regulatory Compliance



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	COATING COLOR
HyFlex® 11-528	Finishing: Palm Coated Coating Material: Nitrile Liner Material: HPPE, Basalt, Polyester, Spandex Cuff Style: Knitwrist	18	6, 7, 8, 9, 10, 11	Black

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.