



Brand of NTN Group

## Technical data


### SES208

Insert bearings



Stainless steel insert, spherical outer diameter, fixing by eccentric locking collar, single lip seal, food grease

### VISUAL (S)



### PRODUCT DEFINITION

<b>Brand</b>	SNR
<b>B - Width of Inner Ring</b>	30,2 mm
<b>B1 - Overall width Inner Ring</b>	43,7 mm
<b>B2 - Width of eccentric locking collar/nut</b>	18,3 mm
<b>C - Width of Outer Ring</b>	18 mm
<b>C1 - Distance center of OR to center of lubrication zone</b>	6,2 mm
<b>d - Shaft diameter</b>	40 mm
<b>d1 - Outer dia of eccent. Lock. collar / nut of adapter sleeve</b>	60,3 mm



**NTN Europe**

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

### PRODUCT DEFINITION

<b>D - Outer diameter of OR</b>	80 mm
<b>G - Set screw size</b>	M8x1
<b>m - Distance to set screw</b>	6,5 mm
<b>r - Radius Inner Ring</b>	1
<b>S - Distance front side/bearing centre</b>	9 mm
<b>f0 - Factor</b>	13.7
<b>SW - Wrench size</b>	4 mm

### PRODUCT PERFORMANCE

<b>C - Dynamic load rating</b>	32000000 mN
<b>C0 - Static load rating</b>	19300000 mN
<b>Operating temperature min.</b>	253,15 °K
<b>Operating temperature max.</b>	373,15 °K

### OTHER FEATURES

<b>Mass</b>	0,64 kg
<b>Recommended tightening torque for set screw</b>	8.3 N-m

### BEARING FREQUENCIES

<b>BPFO - Over rolling frequency on outer ring (60 rpm)</b>	3.547 Hz
<b>BPFI - Over rolling frequency on inner (60 rpm)</b>	5.452 Hz
<b>BSF - Over rolling frequency on rolling element (60 rpm)</b>	4.513 Hz
<b>BRF - Rotational frequency - rolling element (60 rpm)</b>	2.2565 Hz
<b>FTF - Rotational frequency - cage (60 rpm)</b>	0.394 Hz

