

8098
lifting chain sling, 4 legs with clevis grab hooks, grade 8

CE

EN 818-4

TECHNICAL DATA

- safety factor: 4
- chain-sling identification tag

ATTACHED CERTIFICATES

- Manufacturer's Certificate UNI EN818-4
- CE Declaration of Conformity

AVAILABLE CERTIFICATES

- Technical product specifications



	art.	 D mm	L m	WLL ton
080980001	8098 D6-1	6*	1	2,36
080980002	8098 D6-2	6*	2	2,36
080980003	8098 D6-3	6*	3	2,36
080980004	8098 D6-4	6*	4	2,36
080980021	8098 D7-1	7*	1	3,15
080980022	8098 D7-2	7*	2	3,15
080980023	8098 D7-3	7*	3	3,15
080980024	8098 D7-4	7*	4	3,15
080980041	8098 D8-1	8*	1	4,25
080980042	8098 D8-2	8*	2	4,25
080980043	8098 D8-3	8*	3	4,25
080980044	8098 D8-4	8	4	4,25
080980051	8098 D10-1	10*	1	6,7
080980052	8098 D10-2	10	2	6,7
080980053	8098 D10-3	10	3	6,7
080980054	8098 D10-4	10	4	6,7
080980131	8098 D13-1	13	1	11,2
080980132	8098 D13-2	13	2	11,2
080980133	8098 D13-3	13	3	11,2
080980134	8098 D13-4	13	4	11,2
080980161	8098 D16-1	16	1	17
080980162	8098 D16-2	16	2	17
080980163	8098 D16-3	16	3	17
080980164	8098 D16-4	16	4	17
080980172	8098 D20-2	20	2	26,5
080980173	8098 D20-3	20	3	26,5
080980174	8098 D20-4	20	4	26,5