

# Hynit®

## 32815

Nitrile impregnated sewn glove



Oil



Light Duty

## Nitrile-impregnated, abrasion-resistant gloves offering dexterity and liquid repellence

- **Improved durability and flexibility:** Hynit® 32-815 hand protection gloves feature a special nitrile formulation that combines excellent abrasion protection and flexibility
- **Increased durability:** These protective gloves' liquid-repellent impregnation guards against oil, grease and dirt
- **Elevated comfort:** In addition, these nitrile disposable gloves' polycotton liner keeps hands comfortable and dexterous



### Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Construction
- Logistics
- Recycling and Waste Disposal
- Warehousing

### Applications

- Assembly of white goods
- Raw material handling
- Packaging
- Product shipping, transport and delivery
- Steel bars, sheet metals, cans and other metal products
- General handling
- Semiconductor manufacturing
- Maintenance



# 32815

## Nitrile impregnated sewn glove

### Key Features

- **Special nitrile formulation:** Superior durability and flexibility
- **Liquid-repellent impregnation:** Protects from oil, grease and dirt
- **Polycotton liner:** Combines comfort with dexterity

### Vulcanization Chemical Accelerators

- Natural rubber proteins

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

### Performance Standards & Regulatory Compliance



### Specifications

| BRAND   STYLE | DESCRIPTION                                                                                                                              | Gauge | SIZE             | LENGTH                        | COATING COLOR | PACKAGE                      |
|---------------|------------------------------------------------------------------------------------------------------------------------------------------|-------|------------------|-------------------------------|---------------|------------------------------|
| Hynit® 32-815 | <b>Finishing:</b> Palm Coated<br><b>Coating Material:</b> Nitrile<br><b>Liner Material:</b> Polycotton<br><b>Cuff Style:</b> Safety Cuff |       | 7, 7.5, 8, 9, 10 | 240-265 mm; 9.45-10.43 inches | Blue          | 12 pairs/bag, 12 bags/carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306.  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

