





UD18-XX-XX-SS


Ruland UD18-XX-XX-SS, Machinable Bore Double Universal Joint, Friction Bearing, Steel, 1.120" (28.4mm) OD, 5.125" (130.2mm) Length



Description

Ruland UD18-XX-XX-SS is a double cardan friction bearing universal joint with plain bores that can be machined to a bore size and geometry of the user's choice. It has a 1.120" (28.4mm) OD and 5.125" (130.2mm) length. UD18-XX-XX-SS is ideal for applications with wide distances between shafts and can accommodate all forms of misalignment. This plain bearing double universal joint is comprised of pins and blocks that are precision machined, selectively heat treated, and ground for high strength, accuracy, and wear resistance. The combination of these components with precision ground and hardened yoke ears allow for a longer lifespan, increased performance in demanding applications, and greater angular misalignment of up to 90° when compared to commodity style double universal joints. UD18-XX-XX-SS is made from high grade stainless steel for increased corrosion resistance. It can be combined with boot UBOOT18/29-NI-KIT to protect the joints from unwanted contaminants such as dust or water and self lubricate reducing maintenance time. This double cardan universal joint is manufactured in the USA by Belden Universal for strict control of processes.

Product Specifications

Bore (B1)	No Bore	Small Bore (B2)	No Bore
B1 Max Shaft Penetration	1.220 in (31.0 mm)	B2 Max Shaft Penetration	1.220 in (31.0 mm)
Joint Outer Diameter (OD)	1.120 in (28.4 mm)	Length (L)	5.125 in (130.2 mm)
Center Yoke Length (LC)	1.625 in (41.3 mm)	Yoke Length (LY)	1.750 in (44.5 mm)
Hub Depth (LH)	1.220 in (31.0 mm)	Max Round Bore (Inch)	0.625 in
Max Round Bore (Metric)	15 mm	Max Hex or Square Bore (Inch)	0.6250 in
Max Hex or Square Bore (Metric)	14 mm	Max Blind Bore (Inch)	0.8750 in
Max Blind Bore (Metric)	22 mm	Max Round Bore w/ Key (Inch)	5/8" Bore, 3/16" Keyway
Max Round Bore w/ Key (Metric)	16mm Bore, 5mm Keyway	Peak Torque	2025 in-lb (228.8 Nm)
Rated Torque	405 in-lb (45.8 Nm)	Max Operating Angle	90°
Material Specification	Yokes: 303 Stainless Steel Pins and Blocks: 416 Stainless Steel	Manufacturer	Belden Universal
Country of Origin	USA	Weight (lbs)	1.216000
Recommended Lubricant	LUBRIPLATE No. 1200-2	Matching Boot Cover	UBOOT18/29-NI-KIT
UPC	634529288481	Tariff Code	8483.60.4000
UNSPC	25173810		
Note 1	Performance ratings are for guidance only. The user must determine suitability for a particular application.		
Prop 65	 WARNING This product can expose you to the chemical Nickel (metallic), known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov .		