

## Han High Temp 24B Base Panel 2 levers



Image is for illustration purposes only. Please refer to product description.

Part number	09 62 824 0391
Specification	Han High Temp 24B Base Panel 2 levers
HARTING eCatalogue	<a href="https://harting.com/09628240391">https://harting.com/09628240391</a>

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han® High Temp
Type of hood/housing	Bulkhead mounted housing
Type	Low construction

### Version

Size	24 B
Locking type	Double locking lever

### Technical characteristics

Tightening torque	1 Nm Fixing screws M4
Limiting temperature	-40 ... +200 °C With Han® High Temp components
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
Material (seal)	FPM
Colour (seal)	Red
Material (locking)	Stainless steel
RoHS	compliant



**Pushing Performance**  
Since 1945

## Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

## Commercial data

Packaging size	1
Net weight	171.16 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140074231
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466