

# 15U Wallmount Server Rack with Adjustable Rails

Product ID: RK15WALLOA



This open frame wallmount server rack provides 15U of storage, helping you to save space and stay organized. The equipment rack features an adjustable depth and can hold a total of up to 198 lb (90 kg).

## Accommodate Larger Devices

The open frame rack adjusts from 12 to 20 inches (30.4 to 50.8 cm) to accommodate larger data, network, and telecommunication devices. The above-average depth also gives you the option to mount shelves and other accessories.

## Free up Floor Space

When space is limited you can wall-mount the open-frame rack in a server room, office, or above a doorway, to expand your workspace and ensure your equipment is easy to access.

## **Keep Equipment Cool and Accessible**

The rack's open frame design promotes passive cooling; ensures easy access to your rack-mounted equipment and makes it simple to configure mounted devices, which saves you time.

## **Easy, Hassle-Free Installation**

With an adjustable depth as low as 12 inches (30.4 cm), this network rack is perfect for smaller spaces. It's easy to assemble and features wall-mounting holes that are spaced 12 and 16 in. apart, making it suitable for mounting on almost any wall, based on North American wall-frame stud-spacing standards.

### Certifications, Reports and Compatibility



### Applications

- Small office spaces
- When floor space is limited

### Features

- Accommodate a range of device sizes with the adjustable depth and a weight capacity of 198 lbs. (90kg)
- Fits into smaller spaces and frees up floor space when mounted to the wall
- Provides passive cooling for equipment with the open frame wall mount rack design
- Easy installation with the standard 12 and 16 inch mounting holes accommodating standard stud spacing

<b>Hardware</b>	Warranty	5 Years
	Frame Type	Open Frame
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	L-Shape
	Rack Type	2-Post
	Special Features	Adjustable Mounting Rails
		Easy Assembly
		U-Markings
U Height	15U	
Wallmountable	Yes	
<b>Performance</b>	External Depth Range	30.5 cm to 50.8 cm (12 inches to 20 inches)
	Internal Depth Range	30 cm to 50.3 cm (11.8 inches to 19.8 inches)
	Weight Capacity	198.9 lb [90 kg]
<b>Physical Characteristics</b>	Color	Black
	Construction Material	Steel
	Maximum Mounting Depth	19.9 in [50.6 cm]
<b>Product Measurements</b>	Product Height	30.4 in [77.3 cm]
	Product Length	20.1 in [51 cm]
	Product Width	19.8 in [50.4 cm]
	Weight of Product	33.5 lb [15.2 kg]
<b>Packaging Information</b>	Flat Pack (Assembly Required)	Yes
	Package Height	5.1 in [13 cm]
	Package Length	31.5 in [80 cm]
	Package Width	20.9 in [53 cm]
	Shipping (Package) Weight	39.3 lb [17.8 kg]
<b>What's in the Box</b>	Included in Package	2 - Vertical Rails
		2 - Front Horizontal Brackets
		2 - Rear Horizontal Brackets

60 - M6 Cage Nuts

60 - M6 Screws

60 - Plastic Washers

16 - Assembly Screws

24 - Flat Washers

24 - Bolts

1 - User Manual

---

Product appearance and specifications are subject to change without notice.