

# Metal drill bits HSS PointTeQ

| PRODUCT PROPERTIES |                   |                 |                       |                   | ORDERING INFORMATION |               |                        |               |               |
|--------------------|-------------------|-----------------|-----------------------|-------------------|----------------------|---------------|------------------------|---------------|---------------|
| Diameter (D) mm    | Working length mm | Total length mm | Shank diameter (d) mm | Diameter (D) Inch | Packaging type       | Pack quantity | Minimum order quantity | Barcode       | Part number   |
| 5                  | 52                | 86              | 5                     | -                 | PC1d                 | 1             | 5                      | 3165140906746 | 2 608 577 165 |
| 5.5                | 57                | 93              | 5.5                   | -                 | PC1d                 | 1             | 5                      | 3165140906753 | 2 608 577 166 |
| 6                  | 57                | 93              | 6                     | -                 | PC1d                 | 1             | 5                      | 3165140906760 | 2 608 577 167 |
| 6.5                | 63                | 101             | 6.5                   | -                 | PC1d                 | 1             | 5                      | 3165140906777 | 2 608 577 168 |
| 7                  | 69                | 109             | 7                     | -                 | PC1d                 | 1             | 5                      | 3165140906784 | 2 608 577 169 |
| 7.5                | 69                | 109             | 7.5                   | -                 | PC1d                 | 1             | 5                      | 3165140906791 | 2 608 577 170 |
| 8                  | 75                | 117             | 8                     | -                 | PC1d                 | 1             | 5                      | 3165140906807 | 2 608 577 171 |
| 8.5                | 75                | 117             | 8.5                   | -                 | PC1d                 | 1             | 5                      | 3165140906814 | 2 608 577 172 |
| 9                  | 81                | 125             | 9                     | -                 | PC1d                 | 1             | 5                      | 3165140906821 | 2 608 577 173 |
| 10                 | 87                | 133             | 10                    | -                 | PC1d                 | 1             | 5                      | 3165140906838 | 2 608 577 174 |
| 11                 | 94                | 142             | 11                    | -                 | PC1d                 | 1             | 5                      | 3165140906845 | 2 608 577 175 |
| 12                 | 101               | 151             | 12                    | -                 | PC1d                 | 1             | 5                      | 3165140906852 | 2 608 577 176 |
| 13                 | 101               | 151             | 13                    | -                 | PC1d                 | 1             | 5                      | 3165140906869 | 2 608 577 177 |

Pack of 10

|     |    |    |     |   |     |    |   |               |               |
|-----|----|----|-----|---|-----|----|---|---------------|---------------|
| 1   | 12 | 34 | 1   | - | P2a | 10 | 1 | 3165140906876 | 2 608 577 178 |
| 1.1 | 14 | 36 | 1.1 | - | P2a | 10 | 1 | 3165140906883 | 2 608 577 179 |
| 1.2 | 16 | 38 | 1.2 | - | P2a | 10 | 1 | 3165140906890 | 2 608 577 180 |
| 1.3 | 16 | 38 | 1.3 | - | P2a | 10 | 1 | 3165140906906 | 2 608 577 181 |
| 1.4 | 18 | 40 | 1.4 | - | P2a | 10 | 1 | 3165140906913 | 2 608 577 182 |
| 1.5 | 18 | 40 | 1.5 | - | P2a | 10 | 1 | 3165140906920 | 2 608 577 183 |
| 1.6 | 20 | 43 | 1.6 | - | P2a | 10 | 1 | 3165140906937 | 2 608 577 184 |
| 1.7 | 20 | 43 | 1.7 | - | P2a | 10 | 1 | 3165140906944 | 2 608 577 185 |
| 1.8 | 22 | 46 | 1.8 | - | P2a | 10 | 1 | 3165140906951 | 2 608 577 186 |
| 1.9 | 22 | 46 | 1.9 | - | P2a | 10 | 1 | 3165140906968 | 2 608 577 187 |
| 2   | 24 | 49 | 2   | - | P2a | 10 | 1 | 3165140906975 | 2 608 577 188 |
| 2.1 | 24 | 49 | 2.1 | - | P2a | 10 | 1 | 3165140906982 | 2 608 577 189 |
| 2.2 | 27 | 53 | 2.2 | - | P2a | 10 | 1 | 3165140906999 | 2 608 577 190 |
| 2.3 | 27 | 53 | 2.3 | - | P2a | 10 | 1 | 3165140907002 | 2 608 577 191 |
| 2.4 | 30 | 57 | 2.4 | - | P2a | 10 | 1 | 3165140907019 | 2 608 577 192 |
| 2.5 | 30 | 57 | 2.5 | - | P2a | 10 | 1 | 3165140907026 | 2 608 577 193 |
| 2.6 | 30 | 57 | 2.6 | - | P2a | 10 | 1 | 3165140907033 | 2 608 577 194 |
| 2.7 | 33 | 61 | 2.7 | - | P2a | 10 | 1 | 3165140907040 | 2 608 577 195 |
| 2.8 | 33 | 61 | 2.8 | - | P2a | 10 | 1 | 3165140907057 | 2 608 577 196 |
| 2.9 | 33 | 61 | 2.9 | - | P2a | 10 | 1 | 3165140907064 | 2 608 577 197 |
| 3   | 33 | 61 | 3   | - | P2a | 10 | 1 | 3165140907071 | 2 608 577 198 |
| 3.1 | 36 | 65 | 3.1 | - | P2a | 10 | 1 | 3165140907088 | 2 608 577 199 |
| 3.2 | 36 | 65 | 3.2 | - | P2a | 10 | 1 | 3165140907095 | 2 608 577 200 |
| 3.3 | 36 | 65 | 3.3 | - | P2a | 10 | 1 | 3165140907101 | 2 608 577 201 |
| 3.4 | 39 | 70 | 3.4 | - | P2a | 10 | 1 | 3165140907118 | 2 608 577 202 |
| 3.5 | 39 | 70 | 3.5 | - | P2a | 10 | 1 | 3165140907125 | 2 608 577 203 |
| 3.6 | 39 | 70 | 3.6 | - | P2a | 10 | 1 | 3165140907132 | 2 608 577 204 |
| 3.7 | 39 | 70 | 3.7 | - | P2a | 10 | 1 | 3165140907149 | 2 608 577 205 |
| 3.8 | 43 | 75 | 3.8 | - | P2a | 10 | 1 | 3165140907156 | 2 608 577 206 |
| 3.9 | 43 | 75 | 3.9 | - | P2a | 10 | 1 | 3165140907163 | 2 608 577 207 |
| 4   | 43 | 75 | 4   | - | P1h | 10 | 1 | 3165140907170 | 2 608 577 208 |
| 4.1 | 43 | 75 | 4.1 | - | P1h | 10 | 1 | 3165140907187 | 2 608 577 209 |
| 4.2 | 43 | 75 | 4.2 | - | P1h | 10 | 1 | 3165140907194 | 2 608 577 210 |
| 4.3 | 47 | 80 | 4.3 | - | P1h | 10 | 1 | 3165140907200 | 2 608 577 211 |
| 4.4 | 47 | 80 | 4.4 | - | P1h | 10 | 1 | 3165140907217 | 2 608 577 212 |
| 4.5 | 47 | 80 | 4.5 | - | P1h | 10 | 1 | 3165140907224 | 2 608 577 213 |
| 4.6 | 47 | 80 | 4.6 | - | P1h | 10 | 1 | 3165140907231 | 2 608 577 214 |
| 4.7 | 47 | 80 | 4.7 | - | P1h | 10 | 1 | 3165140907248 | 2 608 577 215 |
| 4.8 | 52 | 86 | 4.8 | - | P1h | 10 | 1 | 3165140907255 | 2 608 577 216 |
| 4.9 | 52 | 86 | 4.9 | - | P1h | 10 | 1 | 3165140907262 | 2 608 577 217 |
| 5   | 52 | 86 | 5   | - | P1h | 10 | 1 | 3165140907279 | 2 608 577 218 |