

A48.10.100 0...80°C L1=160x9mm copper alloy CL.2

Bimetallic thermometer TYP48-50

Item number: 3903273

Quantity: 1 pcs.

Order code: A48.10.100-G-C1D-160DMZZFV-1ZZZZZZZBK-ZZZ

2BZTM4801

Overview: A48.10.100 0...80°C L1=160x9mm copper alloy CL.2

Case material: aluminium

Pointer: plastic, black Window: acrylic, (SAN)

galvanised steel flange, adjustable on stem, diameter of pitch circle 51mm/D61mm

Dial background: white

WIKA

Data sheet: TM48.01

Details: Bimetallic thermometer TYP48-50

Model: A48 For air conditioning and ventilation technology

Design: standard, aluminium case

Nominal size [NG, d1]: 100 mm

Case material: aluminium

Unit: °C

Scale range: 0 °C ... 80 °C

Insertion length L1: 160 mm

Stem diameter: 9 mm

Stem material: copper alloy

Process connection: galvanised steel flange, adjustable on stem, diameter of pitch circle 51mm/D61mm

Manufacturer logo: *WIKA*

Pointer: plastic, black

Window: acrylic, (SAN)

Accuracy class: class 2 per EN 13190

Dial background: White

Data sheet: TM48.01