

18V XR BRUSHLESS 3 SPEED OSCILLATING SPEED MULTI-TOOL - 2 X 5AH
DCS356P2



35 pc Accessory Set to support a range of cutting and sanding applications

Depth Control Straight Cut Guide increases cutting accuracy for detailed work

Bright LED light illuminates dark work surfaces for accurate cutting

OVERVIEW

35 pc Accessory Set to support a range of cutting and sanding applications

Depth Control Straight Cut Guide increases cutting accuracy for detailed work

Bright LED light illuminates dark work surfaces for accurate cutting

DUAL-GRIP Variable Speed Trigger provides the ultimate speed and application control

Dust Extraction Adapter AirLock ready or std.35mm

SPECIFICATIONS

Battery Capacity	5 Ah
Length	310 mm
Weight	1.1 kg
Sound Pressure	86 dB(A)
Sound Pressure Uncertainty	3 dB(A)
Sound Power	97 dB(A)
Sound Power Uncertainty	3 dB(A)
Hand/Arm Vibration	12.4 m/s2