


Capacitor, film, Metallized Polypropylene, 20 uF, +/-5% Tol, -40/+85C, Power, 250 VAC



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	42	NOM
H	45	NOM
T	30	NOM
S	37.5	+/-0.4
S1	20.3	+/-0.4
LL	6	-2

Notes:
-F = 1.2 nom

General Information

Supplier:	KEMET
Dielectric:	Metallized Polypropylene
Application:	Power
Style:	Radial Box
Features:	Switching
RoHS:	Yes

Specifications

Capacitance:	20 uF
Voltage:	400 V
Tolerance:	+/-5%
Voltage AC:	250 VAC
Rated Temperature:	70C
Temperature Range:	-40/+85C
Dissipation Factor:	0.05%
Maximum dVdT:	50 v/us
Current/Ripple Current:	29 Amps (100kHz 70C)
Current/Ripple Current:	1004 Amps (Peak)
Resistance/ESR:	1.4 mOhms (100kHz)

Packaging Specifications

Package Kind:	Bulk
Package Quantity:	36