

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [120086-0206](#)
Status: **Active**
Overview: [Brad® Nano-Change® (M8) Products](#)
Description: Nano-Change® (M8) Single-Ended Cordset, 5 Poles, Male (Straight) to Pigtail, 24 AWG, PUR Cable, 2.0m (6.56') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E152210

General

Product Family Industrial Cordsets
 Series [120086](#)
 Connector End A Nano-Change® (M8)
 Connector End B Pigtail
 IP Rating IP68
 Overview [Brad® Nano-Change® (M8) Products](#)
 Product Name Nano-Change® (M8)
 Protocol N/A
 Region America
 Type Single Ended
 UPC 78678832989

Physical

Cable Diameter 5.08mm (.200")
 Cable Length 2.0m (6.56')
 Color - Cable Jacket Yellow
 Coupling Style Threaded
 Gender Male-Pigtail
 LED Indicator No
 Material - Cable Jacket PVC
 Material - Connector Body TPE
 Material - Contact Copper Alloy
 Material - Coupling Nut Nickel-plated Brass
 Material - O-Ring Viton
 Material - Plating Mating Gold
 Orientation Straight
 Poles 5
 Temperature Range - Operating -20°C to +105°C
 Wire Size AWG 24
 Wire/Cable Type UL 2661

Electrical

Current - Maximum per Contact 3A
 Voltage - Maximum 60V AC / 75V DC

Material Info

Old Part Number 405006A10M020

Reference - Drawing Numbers

Sales Drawing SD-120027-002, SD-120086-132



EU RoHS

**ELV and RoHS
 Compliant**
**REACH SVHC
 Not Reviewed**
**Low-Halogen Status
 Not Reviewed**

China RoHS



**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

120086Series

This document was generated on 02/04/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION