



## DCS331M2

### 18V XR Li-Ion Jigsaw

#### Selling Proposition

- Powerful & highly efficient DEWALT PM47 fan-cooled motor with replaceable brushes. delivers fast cutting action up to 3000 strokes per minute maximising user productivity
- Intelligent variable speed trigger & lock-off switch for quick controlled cuts and enhanced work safety
- Tool-free adjustable shoe with anti-scratch cover bevels 45 degrees in both directions
- Quick and easy patented keyless blade change system, accepts T-shank blades
- Patented anti-vibration counter-balance mechanism and rubber grip providing a smooth operation
- 3-position pendulum action controls the aggressiveness or smoothness of cuts

#### Standard Equipment

- Anti-scratch shoe cover
- Dust port
- Multi-voltage charger
- 2 x 4.0Ah XR Li-Ion battery packs with state of charge indicator
- Heavy duty kit box

#### Warranty Specifications

- 3 year limited warranty
- 30 Day No Risk Satisfaction Guarantee
- 1 Year Free Service Contract

Specifications	
Battery chemistry	XR Li-Ion
Voltage	18 V
Battery Capacity	4.0 Ah
Power Output	400 Watt
No Load Stroke Rate	0-3000 spm
Stroke Length	26 mm
Bevel Capacity	45 °
Max. Depth of Cut [Wood]	135 mm