

Product data sheet

Specifications



Spacial SF 1 entry cable gland plate - fixed by clips - 1200x600 mm

NSYEC1261

Main

Range	Spacial
Product or component type	Cable gland plate
Accessory / separate part category	Cable management accessory
Anwendung	Multi-purpose
Range compatibility	Spacial SF
Mounting location	Enclosure bottom
Cable gland type	Standard
Cable entry	1 entry
Device composition	fixing elements 1 plate self extinguishing polyurethane adhesive gasket with cross-section of 15 x 25 mm
Quantity per set	Set of 1
Material	Galvanised steel

Complementary

Height	35 mm
Width	1200 mm nominal: 1016 mm useful:
Depth	600 mm nominal: 520 mm real:
Thickness	1.5 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	7.019 kg
Package 1 Height	3 cm
Package 1 width	34 cm
Package 1 Length	51.5 cm
Unit Type of Package 2	PAM
Number of Units in Package 2	40

Package 2 Weight	293.76 kg
Package 2 Height	45 cm
Package 2 width	100 cm
Package 2 Length	120 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------