
BCC M333-0000-20-000-13X350-000

Order Code: BCC0HLW





C € EHI ⊠

Basic features		Environmental conditions	
Approval/Conformity	CE EAC WEEE	Ambient temperature IP rating	-2580 °C IP67
Electrical connection		Material	
		Material contact carrier	PA
Cable diameter D	2.55.2 mm	Material contacts	Bronze
Connection	M8x1-Male, Straight, 3-pin, A-	Material cover nut	Die-cast zinc
	coded	Material grip	PA
Number of connectable contacts	3		
System	Can be fabricated	Mechanical data	
Electrical data		Connection cross-section	0.250.5 mm ²
O	001/00/001/00	Tightening torque pigtail	0.6 Nm
Operating voltage Ub	60 VDC / 60 VAC	Type of wire mounting	IDC
Rated current (40 °C)	4.0 A		
Remarks			

Remarks

Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

##