

Leitz Ergo Cosy Standing Desk Converter with sliding tray



The Leitz Ergo Cosy Standing Desk Converter with sliding tray for keyboard and mouse allows the flexibility to move between sitting and standing while you work, encouraging muscle movement, improving posture and increasing energy levels. Quick and easy to set-up, this desk riser will transform your workspace instantly and remains strong and stable at any height. The pneumatic assisted adjustment will effortlessly lift the stand to the perfect height, moving straight up and down within its own footprint to save space. With its minimalist and modern design, this stylish sit stand desk converter will improve health and wellbeing by creating the perfect active working set-up. Combine with other Leitz Ergo products for an inviting and flexible workspace that keeps you moving all day.



Attributes

- Stylish and ergonomically designed standing desk converter with sliding tray for keyboard and mouse to keep you active all day
- Switch between sitting and standing to promote muscle movement for overall health and wellbeing
- Pneumatic assisted height adjustment to switch easy and effortlessly between sitting and standing positions
- Tested and recommended by the German IGR Institute for Health and Ergonomics, according to DIN 26800 EN ISO 15537 - also TÜV and GS certified
- Workstation moves straight up and down within its own footprint to save space
- Holds a monitor and a laptop with stand on the main converter desk surface and the sliding tray holds a keyboard and mouse with space for wrist rests
- Ultra-compact 800 x 420 mm footprint so it will not take up too much space on your desk
- Slim design makes it easy to carry and store when not in use
- Minimum height 72 mm, maximum height 380 mm
- Supports up to 16 kg on main desk surface & up to 8 kg on the keyboard & mouse sliding tray
- 5 years guarantee
- Plastic free packaging and product arrives fully assembled



Specifications

Number	65320085
Colour	grey
Dimensions (W x H x D)	420 x 72 x 800 mm
Weight	16020 g
Pallet quantity	10
EAN code	4002432129430