

Datasheet

RS Pro Extra slim led spotlight 30W

Remote controlled

RS Stock No: 1363570



Specifications :

This outdoor spotlight has a surprising design. Not only it is built in a frame barely 38mm thick, but its LED technology allows delivering an impressive power: 2400 lumens.

Sensor detection is integrated in the front face and allows self-igniting. The latter is totally customizable because of a smart remote control. At the push of a single button you can adjust the lighting times and its mode of operation.

Its modern Black design is very simple and offers a considerable discretion. Extra slim, this spotlight can be also installed close to a front door, a garage door as well as a wall alongside an alley. Its lighting angle of 120° is wide and very comfortable.

Its high level of performance has been made possible by the use of quality electronics and a COB led capable of generating a powerful light and a very beautiful purity. Despite its power, this projector is energy efficient: its consumption does not exceed 30W.

A 40cm white offset arm, as an option (1363567).

Features :

- Power supply consumption: 30W
- Lighting power:
- Cool Daylight. : 2400 lumens
- Lighting colour: Cool Daylight 6000K
- Dimension (h x l x p):
200 x 155 x 38 mm