

## DCF900H2T-QW

Boulonneuse 1/2" XR 18V 5Ah Li-Ion Brushless 1396 Nm – Jonc de sécurité - POWERSTACK



5035048806425



### Product Description:

Max. Tightening Torque (Nm): 1396Max. Peeling Torque (Nm): 1898No-Load Speed (RPM): 0-650/1000/2300Tool Holder: 1/2"Max. Bolt Ø: M30Impacts Per Minute (imp/min): 0-2200Length (mm): 223

### Product features and benefits:

- Latest generation XR 18V nutrunner with high torque Performance:
- Loosening torque of up to 1898 Nm ensures the removal of the tightest bolts O'Ring fastening: quick socket changes Full speed and brightness
- control on all applications: variable speed trigger + touch selection
- function - 4 modes (3 speeds + Precision mode) Work area lighting: Bright white LED with delay function for improved visibility User comfort and control: comfortable rubber grip Brushless motor: more power, efficiency and durability
- 
- 

### Specifications techniques :

- Power: 760 W
- Battery Weight: 0.75 Kg
- Voltage: 18 V

### Product Warranty:

This product has a 1-year warranty extended to 3 years after registration

### Included Items:

- Charger (x1)
- TSTAK Box (x1)

## DCF900H2T-QW

Boulonneuse 1/2" XR 18V 5Ah Li-Ion Brushless 1396 Nm – Jonc de sécurité - POWERSTACK



5035048806425

Part of the DCF900H2T series

Ref	▲ ▼ Title	▲ ▼
DCF900H2T-QW	Boulonneuse 1/2" XR 18V 5Ah Li-Ion Brushless 1396 Nm – Jonc de sécurité - POWERSTACK	