



# 568.1686-RW

## INTERLOCKED SOCKET + RCD

16A 3P+E 6h 380-415V 50Hz 60Hz  
136X390MM Screw terminals With mechanical interlock

Product Approvals

TECHDATA		STANDARDS AND LAWS	
Commercial series	ADVANCE 2 Series	EN 60309-1 (1999)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
Type of product	INTERLOCKED SOCKET + RCD	EN 60309-2 (1999)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 2: Dimensional interchangeability requirements for pin and contact-tube accessories of harmonized configurations
Synthetical description	INTERLOCKED SOCKET + RCD		
Mounting version	SURFACE MOUNTING	DIRECTIVE LOW VOLTAGE 2014/35 /UE	[European Directives] Low Voltage Directive
Rated current	16A		
Poles	3P+E		
Hour position	6h		
Rated voltage (range)	250-400V		
Rated voltage	380-415V		
Working frequency	50Hz		
Working frequency	60Hz		
Colour	RED		
Material	THERMOPLASTIC		
Protection degree	Watertight		
Protection degree IP	IP66/IP67		
Protection degree IK	IK07		
Terminals	Screw terminals		
Flange	136X390MM		

Cable outlet	DRILLING POINT MARK
Options	With mechanical interlock
Notes	WITH DIN RAIL (6 MODULES)
Padlock	ø5mm