





THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AF	50		N	REV PER 0G3A-0254-04	26APR04	JR KR

- 1 CONTINUOUS STRIP ON REELS WITH TERMINALS
LOCATED ON 5.59±0.08 [.220±.003] CENTERS.
- 2 SLOT ACCEPTS 0.45-0.64mm [#25-#22] AWG COPPER MAGNET
WIRE. TWO WIRES OF THE SAME SIZE PER SLOT EXCEPT 0.64
[#22] AWG WHICH IS ONE WIRE ONLY.
- 3 POKE-IN ACCEPTS A 0.50-0.90mm [#20-#18] AWG SOLID OR
FUSED STRANDED LEAD WIRE.
- 4 MEASURE WHEN FREE STATE IS COMPRESSED TO
2.95 [.116] MAX.
- 5 0.002032 [.000080] MIN TIN PLATE.



H04 PHOSPHOR BRONZE	STANDARD	PAPER SPLICE	WITHOUT PAPER EXCEPT IN SPLICE AREAS	5	63658-5
4M BRASS	STANDARD	SPLICE FREE	PLASTIC REEL WITH PAPER	UNPLATED	63658-4
4M BRASS	REVERSE	PAPER SPLICE	WITHOUT PAPER EXCEPT IN SPLICE AREAS	5	63658-3
4M BRASS	STANDARD	SPLICE FREE	PLASTIC REEL WITHOUT PAPER	5	63658-2
4M BRASS	STANDARD	PAPER SPLICE	WITHOUT PAPER EXCEPT IN SPLICE AREAS	5	63658-1
MATERIAL	REELING DIRECTION	SPLICE	REELING MATERIAL	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.A.MAYER 8-10-92	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105			
DIMENSIONS: INCHES		CHK M.S.FEHER 8-11-92				
		APVD TL SHUTTER 8-11-92		NAME TERMINAL, POKE-IN, 300 SERIES MAG-MATE		
		PRODUCT SPEC 108-2012				
MATERIAL SEE TABLE		APPLICATION SPEC 114-2046		SIZE A2	CAGE CODE 00779	
FINISH SEE TABLE		WEIGHT -		DRAWING NO C=63658		
CUSTOMER DRAWING				SCALE 10:1	SHEET 1 OF 1	REV N