



tesapack[®] 4124PVC30

ultra strong

Product Information

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

• Backing material	PVC film	• Total thickness	65 µm
• Type of adhesive	natural rubber		

Properties/Performance Values

• Tensile strength	60 N/cm	• Low noise unwinding	yes
• Adhesive strength	Very high adhesion	• Solvent free	no
• Ageing resistance (UV)	no	• Suitable surfaces	Cardboard
• Hand tearability	no	• Tear resistance	yes

Disclaimer

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit <http://l.tesa.com/?ip=NaN>