

PRODUCT-DETAILS

416MVS6W

Switched interlocked socket-outlet, 6h, 16A, IP67, 3P+N+E



General Information

Extended Product Type	416MVS6W
Product ID	2CMA167842R1000
EAN	7392696678421
Catalog Description	Switched interlocked socket-outlet, 6h, 16A, IP67, 3P+N+E
Long Description	Switched Interlocked Socket Outlet, vertical, earthing sleeve position 6h, rated current 16A, IP67 watertight, 3-poles+neutral+earth, frequency 50-60 Hz, color code Red, Padlockable in OFF position

Ordering

E-Number (Sweden)	E2416934
E-Number (Finland)	2421411
E-Number (Norway)	2416934
EAN	7392696678421
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	1 piece

Dimensions

Product Net Width	120 mm
Product Net Height	149 mm
Product Net Weight	0.7 kg
Mechanical Drawings	9AKK107991A3922

Container Information

Package Level 1 Width	152 mm
Package Level 1 Depth / Length	120 mm
Package Level 1 Height	265 mm
Package Level 1 Gross Weight	0.7 kg
Package Level 1 EAN	7392696678421
Package Level 1 Units	box 1 piece
Package Level 2 Width	800 mm
Package Level 2 Depth / Length	1200 mm
Package Level 2 Height	900 mm
Package Level 2 Gross Weight	107.5 kg
Package Level 2 EAN	7392696074896
Package Level 2 Units	pallet (lift) 125 piece

Environmental

RoHS Status	Following EU Directive 2011/65/EU
-------------	-----------------------------------

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC700005D0001
Environmental Information	2CMC000057M0000
RoHS Information	2CMC700005D0001
REACH Declaration	2CMC700005D0001

Additional Information

Additional Information	3P+N+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	1.5 ... 4 mm ²
Cable Diameter	13 ... 17 mm
Cable Entry Position	Top
Cable Outlets Per Side	1xØ25
Color	Red
Connection Type	Screw
Degree of Protection	IP67
Frequency (f)	50 Hz 60 Hz
Function	Switched interlocked socket outlet, vertical
Housing Material	Thermoplastic (PBT)
Invoice Description	Ind. P&S#416MVS6W
Mounting Holes	171x90
Mounting Type	Vertical
Number of Poles	5
Order Multiple	1 piece
Product Main Type	CMVS

Product Name	Industrial Switched Interlocked Socket Outlet
Protection Type	Switched Interlocked
Rated Current (I_n)	16 A
Rated Voltage (U_r)	200/346 ... 240/415 V
Recommended Screw Driver	PH2
Standards	IEC 60309-1, -2, -4
Sub-Function	Cable entry, knock-outs Ø25mm
Suitable For	Switched Interlocked Socket Outlets, Vertical
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC000030M0001
Installation Manual	2CMC000030M0001
RAL Number	RAL 7001 - Silver Grey

Classifications

eClass	27440510
UNSPSC	39120000

Technical

Wire Size	14 ... 12 AWG
Tightening Torque	WireClamp0.8 N·m

Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Critical & Safe → Switched Interlocked Socket Outlets

